Material RF Measurements


RF Absorber Material Measurements brief notes


E. Chojnacki HOM - 2010



Typical Measurement Error

Significant discontinuity between bands and trend within bands










Typical Measurement Error

Three alumina coax samples, ~99% pure.














Stripline Methods?


- Stripline/Microstrip can provide broadband measurements using a single fixture
- Is there a configuration that is
 - easy to assemble
 - insensitive to dimensional error (clamped plates)
 - easy to calibrate and immerse in LN₂
 - lacktriangle analytic extraction of arepsilon and μ







Quasi-TEM for d<<λ



$$Z_0 = \frac{30\pi}{\sqrt{\varepsilon_e}} \frac{b/W_e}{1 + 0.441 \ b/W_e}$$

where W_e is a value describing the **effective width** of the center conductor:

$$\frac{W_e}{b} = \frac{W}{b} - \begin{cases} 0 & \text{for } W/b > 0.35 \\ (0.35 - W/b)^2 & \text{for } W/b < 0.35 \end{cases}$$

Stripline Method

Line-Line Dielectrometric Method

A Wideband Line—Line Dielectrometric Method for Liquids, Soils, and Planar Substrates. Isabelle Huynen, Catherine Steukers, and Fabienne Duhamel,


IEEE TRANSACTIONS ON INSTRUMENTATION AND MEASUREMENT, VOL. 50, NO. 5, OCTOBER 2001,

http://ieeexplore.ieee.org/ielx5/19/20793/00963208.pdf?tp=&arnumber=963208&isnumber=20793&tag=1

Carbon Nanotube Composites for Broadband Microwave Absorbing Materials,

A. Saib, et al., 2005 European Microwave Conference,

http://ieeexplore.ieee.org/stamp/stamp.jsp?tp=&arnumber=1608849



Details of the apparatus and accuracy of the tests are opaque in both publications.

This method needs validation...




Fig. 5. Real part of the effective permittivity of CNT-poly(∈-caprolactone) (PCL) composite with 0.2 (solid line), 0.35 (dashed line), and 0.5 (dash-doted line) weight percent of CNTs.




Fig. 6. RF conductivity of CNT-poly(e-caprolactone) (PCL) composite with 0.2 (solid line), 0.35 (dashed line), and 0.5 (dash-doted line) weight percent of CNTs.